


# GRAS 45BB-8

Head & Torso for Test of Binaural Hearing Aid, 2-Ch CCP



Connection: Constant Current Power (0 V/CCP)

Channel(s): 2

ANSI: S3.36, S3.25

IEC: 60318-7, 60318-4

ITU-T Rec. P.57 Type 3.3 based on ITU-T Rec. P.58

The 45BB-8 KEMAR Head and Torso with TEDS for test of binaural HA, 2-Ch CCP is an acoustic research tool with built-in ear simulators that simulates the changes that occur to soundwaves as they pass a human head and torso. KEMAR fitted with pinna simulator, ear canal extension, and IEC 60318-4 Ear Simulator resembles the acoustic impedance of the human ear. This KEMAR configuration is suitable for hearing aids using RF communication by using non-metal (POM) ear canal extensions and ear holder plates. Its corresponding LEMO equivalent is [GRAS 45BB-7 KEMAR Head & Torso for Test of Binaural Hearing Aid 2-Ch LEMO](#).

## Introduction

The KEMAR head and torso simulator was introduced by Knowles in 1972 and quickly became the industry standard for hearing-aid manufacturers and research audiologists (visit [KEMAR.us](https://www.kemar.us) to read the full story). It is based on worldwide average human male and female head and torso dimensions. It meets the requirements of ANSI S3.36/ASA58-2012 and IEC 60318-7:2011.

The GRAS 45BB-8 KEMAR Head and Torso has the same dimensions and acoustical properties as the original KEMAR, but has been developed further by GRAS to meet the industry's demand for realistic measurements of hearing aids, headphones and headsets. It provides acoustic diffraction similar to that encountered around the median human head and torso, both in the proximity and in the far-field.

As all the preconfigured 45BB KEMARs consist of the same basic 45BB KEMAR Non-configured, plus a set of application-specific accessories, the full information about a given KEMAR configuration is obtained by combining the information about the 45BB KEMAR Non-configured and the information for a given configured version as found in the present text. Read about the non-configured KEMAR [here](#).

## TEDS Compatibility

All CCP-based KEMAR configurations are IEEE 1451.4 TEDS v. 1.0 compliant. If your measurement platform supports Transducer Electronic Data Sheets (TEDS), you will be able to read and write data like properties and calibration data.

## Design

The 45BB-8 is a KEMAR head and torso for binaural hearing aid test, with prepolarized ear simulators and large 55 Shore 00 pinnae. A special feature is

that the ear holder plates, ear canal extensions, and accompanying screws are made of POM, Nylon, and Teflon to allow RF signals to pass inside KEMAR's head.

It is delivered fully configured, individually calibrated and ready for use. In addition to a system calibration certificate, a USB flash memory with simulation data is included.

Apart from the abovementioned use of plastic materials, the main configuration-specific components of the 45BB-8 are the GRAS RA0045-S1 Ear Simulator According to 60318-4 and the KB0066/KB50065 large pinnae.

### *The 60318-4 Ear Simulator*

The acoustic input impedance of the RA0045-S1 Ear Simulator closely resembles that of the human ear and, as a result, loads a sound source in very much the same way.

It complies with IEC 60318-4 and is measured and calibrated according to ITU-T P.57. It embodies a number of carefully designed volumes connected via well-defined and precisely tuned resistive grooves. In an equivalent electrical circuit, capacitors would represent the volumes, and inductance and resistance would represent respectively air mass and air flow within the resistive grooves.

Read more about RA0045-S1 [here](#).

### *The KB0065/KB0066 Pinna*

The KB0065 and KB0066 are large straight pinnae for use with a straight ear canal extension. The hardness is 55 Shore 00. They comply with the IEC and ITU-T recommendations.

Other accessories for this configuration are listed in

the Ordering Info tab.

## **Performance and warranty**

KEMAR is made of components from our standard portfolio, all manufactured of high-quality material and branded parts chosen and processed to ensure life-long stability and robustness. This enables us to offer a two-year warranty against defective materials and workmanship.

Exceptions: Microphones included in KEMAR as for these our normal five-year warranty apply. The warranty period for cables is six months.

|   |             |   |
|---|-------------|---|
| Connector type  |             | BNC   |
| Set sensitivity @ 250 Hz ( $\pm 2$ dB)  | mV/Pa       | 12.5  |
| Set sensitivity @ 250 Hz ( $\pm 2$ dB)  | dB re 1V/Pa | -38.5   |
| Theoretical dynamic range lower limit with GRAS preamplifier                                      | dB(A)       | 25  |
| Theoretical dynamic range upper limit with GRAS preamplifier @<br>+28 V / $\pm 14$ V power supply | dB          | 151   |
| Theoretical dynamic range upper limit with GRAS CCP preamplifier                                  | dB          | 146   |
| Resonance frequency   | kHz         | 13.5  |
| Temperature range, operation  | °C / °F     | -30 to 60 / -22 to 140                            |
| Temperature range, storage  | °C / °F     | -40 to 65 / -40 to 149                            |
| Humidity range non condensing   | % RH        | 0 to 95%  |
| ANSI standard   |             | S3.36, S3.25                                      |
| IEC standard  |             | 60318-4 (former 60711),<br>60318-7 (former 60959) |
| ITU-T recommendations   |             | P.380   |
| Weight  | g / oz      | 11.45 k / 404                                     |

GRAS Sound & Vibration reserves the right to change specifications and accessories without notice.

## Included items

|                                |  |
|--------------------------------|--|
| <a href="#">GRAS 45BB</a>      | KEMAR Head & Torso, Non-configured                                     |
| <a href="#">GRAS KB0065</a>    | KEMAR Large Right Ear 55 Shore 00                                      |
| <a href="#">GRAS KB0066</a>    | KEMAR Large Left Ear 55 Shore 00                                       |
| GRAS RA0249                    | Straight Ear Canal Extension Kit (made of POM, 2 pcs)                  |
| <a href="#">GRAS RA0045-S1</a> | IEC 60318-4 Ear Simulator (Prepol. version, 2 pcs)                     |
| <a href="#">GRAS 26CS</a>      | 1/4" CCP Short Preamplifier (2 pcs)                                    |
| <a href="#">GRAS RA0001</a>    | Right-angled Adapter for 1/2" Microphone and 1/4" Preamplifier (2 pcs) |
| GRAS GR0408                    | Exterior Ear Canal   |
| GRAS GR0409                    | Union Nut  |
| <a href="#">GRAS AA0018-S</a>  | Microdot- BNC Cable, 35 cm (2 pcs)                                     |
| <a href="#">GRAS AA0035</a>    | BNC-BNC Cable, 3 m (2 pcs)   |

## Optional items

### Power Modules for Externally Polarized Ear Simulators and Microphones

|                           |  |
|---------------------------|--|
| <a href="#">GRAS 12AK</a> | 1-Channel Power Module with gain, filters and SysCheck generator           |
| <a href="#">GRAS 12AD</a> | 1-Channel Power Module   |
| <a href="#">GRAS 12AA</a> | 2-Channel Power Module with gain, filters and SysCheck generator           |
| <a href="#">GRAS 12AR</a> | 2-Channel Power Module   |
| <a href="#">GRAS 12AQ</a> | 2-Channel Universal Power Module with signal conditioning and PC interface |

### Power Modules for Pre-polarized Ear Simulators and Microphones

|                           |  |
|---------------------------|--|
| <a href="#">GRAS 12AL</a> | 1-Channel CCP Power Module with A-weighting filter                         |
| <a href="#">GRAS 12AQ</a> | 2-Channel Universal Power Module with signal conditioning and PC interface |

## For Ear Simulator Calibration

|                             |  |
|-----------------------------|--|
| <a href="#">GRAS 42AP</a>   | Intelligent Pistonphone (250 Hz or 251.2 Hz, 114 dB +/- 0.05 dB) |
| <a href="#">GRAS 42AA</a>   | Pistonphone (250 Hz, 114 dB +/- 0.08 dB)                         |
| <a href="#">GRAS RA0157</a> | 1/2" Calibration Adapter for KEMAR Pinna                         |

## Pinna Simulators

|                             |  |
|-----------------------------|--|
| <a href="#">GRAS KB0060</a> | KEMAR Small Right Ear 55 Shore 00                  |
| <a href="#">GRAS KB0061</a> | KEMAR Small Left Ear 55 Shore 00                   |
| <a href="#">GRAS KB0065</a> | KEMAR Large Right Ear 55 Shore 00                  |
| <a href="#">GRAS KB0066</a> | KEMAR Large Left Ear 55 Shore 00                   |
| <a href="#">GRAS KB1060</a> | KEMAR Small Right Ear, 35 Shore 00                 |
| <a href="#">GRAS KB1061</a> | KEMAR Small Left Ear 35 Shore 00                   |
| <a href="#">GRAS KB1065</a> | KEMAR Large Right Ear 35 Shore 00                  |
| <a href="#">GRAS KB1066</a> | KEMAR Large Left Ear 35 Shore 00                   |
| <a href="#">GRAS KB0090</a> | KEMAR Large Right Ear (VA-Style/SQ) 55 Shore 00    |
| <a href="#">GRAS KB0091</a> | KEMAR Large Left Ear (VA-Style/SQ) 55 Shore 00     |
| <a href="#">GRAS KB1090</a> | KEMAR Large Right Ear (VA-Style) 35 Shore 00       |
| <a href="#">GRAS KB1091</a> | KEMAR Large Left Ear (VA-Style) 35 Shore 00        |
| <a href="#">GRAS KB5000</a> | KEMAR Large Right Anthropometric Pinna 35 Shore 00 |
| <a href="#">GRAS KB5001</a> | KEMAR Large Left Anthropometric Pinna 35 Shore 00  |

## Ear Mould Simulators

|                             |  |
|-----------------------------|--|
| <a href="#">GRAS KB0110</a> | Ear Mould Simulator for 2 mm Inner diameter tubing |
| <a href="#">GRAS KB0111</a> | Ear Mould Simulator for 3 mm Inner diameter tubing |

## Ear Canal Extension and Microphone Holder Kits (kits with 2 pcs and O-rings)

|                             |  |
|-----------------------------|--|
| <a href="#">GRAS RA0237</a> | Straight Ear Canal Extension Kit for KEMAR   |
| <a href="#">GRAS RA0238</a> | VA-tapered Ear Canal Extension Kit for KEMAR |

|             |  |
|-------------|--|
| GRAS RA0239 | Ear canal Extension Kit w. silicone lining for KEMAR                                   |
| GRAS RA0240 | Holder for long 1/2" microphone Kit for KEMAR  |
| GRAS RA0241 | Holder for short 1/2" microphone Kit for KEMAR   |
| GRAS RA0243 | Holder for 1/2" microphone Kit for KEMAR   |
| GRAS RA0244 | O-ring kit for KEMAR, 2 pcs.   |
| GRAS RA0249 | Straight Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test |
| GRAS RA0250 | Tapered Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test  |

## KEMAR Retrofit Kit for Binaural Hearing Aid Test

|                             |   |
|-----------------------------|---|
| <a href="#">GRAS RA0251</a> | KEMAR Retrofit Kit for Binaural Hearing Aid Test:<br>The Kit includes Ear Holder Plates, mounting bolts and the RA0249 and RA0250 Ear Canal Extension Kits. Included items are made of POM, Nylon and Teflon. |
|-----------------------------|---|

## KEMAR Retrofit Kit for Anthropometric Concha and Canal Pinna

|                             |   |
|-----------------------------|---|
| <a href="#">GRAS RA0311</a> | KEMAR Retrofit Kit for Anthropometric Concha and Canal Pinna.<br>The Kit includes Ear Simulator Holder, 2 finger screws and a 3 mm Allen Key. |
|-----------------------------|---|

## Extension Cables

|                             |                     |
|-----------------------------|---------------------|
| GRAS AA0034                 | BNC-BNC Cable, 2 m  |
| <a href="#">GRAS AA0035</a> | BNC-BNC Cable, 3 m  |
| GRAS AA0036                 | BNC-BNC Cable, 5 m  |
| GRAS AA0037                 | BNC-BNC Cable, 10 m |

## Flight Case

|             |                     |
|-------------|---------------------|
| GRAS KM0094 | PELI Case for KEMAR |
|-------------|---------------------|

## Simulation Model of KEMAR

|             |   |
|-------------|---|
| GRAS KB3000 | Simulation Model of KEMAR with large pinnae |
| GRAS KB3001 | Simulation Model of KEMAR with small pinnae |

## Stand for KEMAR

|             |                                      |
|-------------|--------------------------------------|
| GRAS AL0026 | Loudspeaker stand for KEMAR, Ø 35 mm |
|-------------|--------------------------------------|

## Miscellaneous

|             |                   |
|-------------|-------------------|
| GRAS KB0000 | KEMAR Handbook    |
| GRAS KB0010 | T-Shirt for KEMAR |

GRAS Sound & Vibration reserves the right to change accessories without notice.



# GRAS Worldwide

Subsidiaries and distributors in more  
than 40 countries

**HEAD OFFICE, DENMARK**  
**GRAS SOUND & VIBRATION**  
Skovlytoften 33  
2840 Holte  
Denmark  
Tel: +45 4566 4046  
[www.GRASacoustics.com](http://www.GRASacoustics.com)  
[gras@grasacoustics.com](mailto:gras@grasacoustics.com)

**USA**  
**GRAS SOUND & VIBRATION**  
9290 SW Nimbus Avenue  
Beaverton, OR 97008  
Tel: 503-627-0832  
Toll Free: 800-231-7350  
[www.GRASacoustics.com](http://www.GRASacoustics.com)  
[sales-usa@grasacoustics.com](mailto:sales-usa@grasacoustics.com)

**UK**  
**GRAS SOUND & VIBRATION**  
Unit 115, Gibson House,  
Ermine Business Park, Huntingdon,  
Cambridgeshire, PE29 6XU  
Tel: +44 (0) 7762 584 202  
[www.GRASacoustics.com](http://www.GRASacoustics.com)  
[sales-uk@grasacoustics.com](mailto:sales-uk@grasacoustics.com)

**CHINA**  
**GRAS SOUND & VIBRATION**  
Room 315, RuiBo Center(T1)  
Lane683, Shenhong Rd,  
Minhang District,  
Shanghai, China, 201107  
Tel: +86 21 64203370  
[www.GRASacoustics.cn](http://www.GRASacoustics.cn)  
[cnsales@grasacoustics.com](mailto:cnsales@grasacoustics.com)



## About GRAS Sound & Vibration

GRAS is a worldwide leader in the sound and vibration industry. We develop and manufacture state-of-the-art measurement microphones and related equipment for industries where acoustic measuring accuracy and repeatability are of the utmost importance. This includes applications and solutions for customers within the fields of aerospace, automotive, audiology, consumer electronics and other highly demanding industries. GRAS microphones are designed to live up to the high quality, durability and accuracy that our customers have come to expect, trust and require.

GRAS Sound & Vibration is represented through subsidiaries and distributors in more than 40 countries and is part of Axiometrix Solutions, a leading test solutions provider comprised of globally recognized measurement brands. Read more at [www.grasacoustics.com](http://www.grasacoustics.com)

[grasacoustics.com](http://grasacoustics.com)

**GRAS**  
An Axiometrix Solutions Brand