

# GRAS 45BC-10

KEMAR with Mouth Simulator and Anthropometric Pinnae for Headset Test, 2-Ch CCP



Connection: CCP  
Channel(s): 2  
Standards: ANSI: S3.36, S3.25  
IEC: 60318-4, based on 60318-7  
Based on ITU-T Rec. P.57 Type 3.3 and  
ITU-T Rec. P.58  
Special feature: Built-in power amplifier for  
mouth simulator

The 45BC-10 KEMAR with TEDS is configured with anthropometric pinnae and prepolarized IEC 60318-4 Ear Simulators. Due to its design, realistic measurement in a sound environment as experienced by a human being using a headset is possible. In addition, the 45BC-10 is provided with a mouth simulator for testing of the microphone in the headset. Its LEMO equivalent is [GRAS 45BC-9 KEMAR with Mouth Simulator and Anthropometric Pinna for Headset test, 2-Ch LEMO](#).

## Introduction

The KEMAR head and torso simulator was introduced by Knowles in 1972 and quickly became the industry standard for hearing-aid manufacturers and research audiologists (visit [KEMAR.us](https://www.kemar.us) to read the full story). It is based on worldwide average human male and female head and torso dimensions. It meets the requirements of ANSI S3.36/ASA58-2012 and IEC 60318-7:2011.

The current KEMAR Head and Torso has the same dimensions and acoustical properties as the original KEMAR, but has been developed further by GRAS to meet the industry's demand for realistic measurements of hearing aids, headphones and headsets. It provides acoustic diffraction similar to that encountered around the median human head and torso, both in the proximity and in the far-field.

As all the preconfigured 45BB KEMARs consist of the same basic 45BB KEMAR Non-configured, plus a set of application-specific accessories, the full information about a given KEMAR configuration is obtained by combining the information about the 45BB KEMAR Non-configured and the information for a given configured version as found in the present text. Read about the non-configured KEMAR [here](#).

## TEDS Compatibility

All CCP-based KEMAR configurations are IEEE 1451.4 TEDS v. 1.0 compliant. If your measurement platform supports Transducer Electronic Data Sheets (TEDS), you will be able to read and write data like properties and calibration data.

## Design

The 45BC-10 is a KEMAR with prepolarized ear simulators and anthropometric pinnae for 2-channel ear and headphone test.

It is delivered fully configured, individually calibrated and ready for use. In addition to a system calibration certificate, a USB flash memory with simulation data is included.

The main configuration specific components of the 45BC-10 are the GRAS RA0045-S1 Ear Simulator According to 60318-4 and the KB5000/KB50001 Anthropometric Pinnae.

*The 44AA Mouth Simulator according to ITU-T Rec. P51 with built-in power amplifier*

The maximum continuous signal the mouth can produce in 1/3-octave bands is 100dB re. 20 $\mu$ Pa in the frequency range of 100Hz to 16kHz. Its loudspeaker accepts an external signal either directly or via its own built-in power amplifier (when power is applied).

*The 60318-4 Ear Simulator*

The acoustic input impedance of the RA0045-S1 Ear Simulator closely resembles that of the human ear and, as a result, loads a sound source in very much the same way.

It complies with IEC 60318-4 and is measured and calibrated according to ITU-T P.57. It embodies a number of carefully designed volumes connected via well-defined and precisely tuned resistive grooves. In an equivalent electrical circuit, capacitors would represent the volumes, and inductance and resistance would represent respectively air mass and air flow within the resistive grooves.

It is delivered with a built-in [GRAS 40A0](#) 1/2" prepolarized pressure microphone.

Read more about [RA0045-S1 Ear Simulator](#).

*The Anthropometric Pinna*

Compared to the standardized pinna, the anthropometric pinna embodies a number of improvements to the concha and ear canal, combined with increased collapsibility of the helix, and improved mounting. It is made of soft silicone, 35 Shore 00 hardness.

The external shape of the pinna is identical to that of the standardized KEMAR pinna, but concha and ear canal have been modified so that they closely mimic the properties of a real human ear. The ear canal has been extended and is now an integral part of the pinna, which seals directly against the ear simulator. Like the human ear, the ear canal has the 1st and 2nd bend, and the interface with the concha is oval. Fit and insertion consistency are much improved over the cylindrically or conically shaped ear canal extensions that are used with the standardized pinna.

The flexibility of the outer ear has been improved, and when mounting supra-aural and circum-aural headphones the pinna now collapses against the head very much like a human ear.

In addition to the traditional push mounting from the outside, the pinna is secured with two screws from the inside of KEMAR's head. These two screws ensure that the pinna is held firmly in place. Therefore, it seals perfectly against the ear simulator and the head, and it is, therefore, possible to mount and dismount DUTs repeatedly without compromising the seal.

Read more about the [Anthropometric Pinnae](#).

## Typical Applications

The anatomical shape of the pinna makes it possible to achieve an excellent fit and sealing with anatomically shaped in-ear transducers.

Controlling the insertion depth is easy, leading to

good insertion consistency and highly improved repeatability and accuracy of measurements.

The improved fit and seal also means that the low-frequency response is improved. It will allow you to reproduce bass notes, as well as effectively measure (active & passive) attenuation.

Therefore, the 45BC-10 KEMAR is ideal for accurate and repeatable testing of headphones, earphones and in-ear hearing protectors. In addition to this, the built-in mouth simulator makes it ideal for accurate and repeatable testing of headsets.

## Performance and warranty

KEMAR is made of components from our standard portfolio, all manufactured of high-quality material and branded parts chosen and processed to ensure life-long stability and robustness. This enables us to offer a two-year warranty against defective materials and workmanship.

Exceptions: Microphones included in KEMAR as for these our normal five-year warranty applies. The warranty period for cables is six months.

Connector type		BNC
Set sensitivity @ 250 Hz ( $\pm 2$ dB)	mV/Pa	12.5
Set sensitivity @ 250 Hz ( $\pm 2$ dB)	dB re 1V/Pa	-38.5
Theoretical dynamic range lower limit with GRAS preamplifier	dB(A)	25
Theoretical dynamic range upper limit with GRAS preamplifier @ +28 V / $\pm 14$ V power supply	dB	151
Theoretical dynamic range upper limit with GRAS CCP preamplifier	dB	146
Resonance frequency	kHz	13.5
Temperature range, operation	$^{\circ}\text{C}$ / $^{\circ}\text{F}$	-30 to 60 / -22 to 140
Temperature range, storage	$^{\circ}\text{C}$ / $^{\circ}\text{F}$	-40 to 65 / -40 to 149
Humidity range non condensing	% RH	0 to 95%
ANSI standard		S3.36, S3.25
IEC standard		60318-7
ITU-T recommendations		P. 58
Weight	g / oz	11.45 k / 404
MOUTH SIMULATOR		.
Output impedance	$\Omega$	8
Maximum power, continuous	W	10
Maximum power, pulsed 2 sec.	W	50
Input impedance	k $\Omega$	20
Gain	dB	10
Input signal, max.	Vrms	2
Power supply, external	Vdc	24

GRAS Sound & Vibration reserves the right to change specifications without notice.

## Included items

<a href="#">GRAS 45BC</a>	KEMAR Head & Torso with <a href="#">GRAS 44AA Mouth Simulator</a> , non-configured
<a href="#">GRAS KB5000</a>	KEMAR Large Right Anthropometric Pinna 35 Shore 00
<a href="#">GRAS KB5001</a>	KEMAR Large Left Anthropometric Pinna 35 Shore 00
GRAS GR0408	External Ear Canal (for calibration, 2 pcs)
GRAS GR0409	Union Nut (for GR0408, 2 pcs)
GRAS GR1874	Ear Simulator Holder (2 pcs)
<a href="#">GRAS RA0045-S1</a>	IEC 60318-4 Ear Simulator, (Prepol.version, 2 pcs)
<a href="#">GRAS 26CS</a>	1/4" CCP Standard Preamplifier with Microdot Connector, Very Short (2 pcs)
<a href="#">GRAS RA0001</a>	Right Angled Adapter for 1/2" Microphone and 1/4" Preamplifier (2 pcs)
<a href="#">GRAS AA0018-S</a>	Microdot-BNC Cable, 35 cm (2 pcs)
<a href="#">GRAS AA0035</a>	3 m BNC - BNC Cable (2 pcs)
<a href="#">GRAS 46BD</a>	1/4" CCP Pressure Standard Microphone Set
<a href="#">GRAS AA0070</a>	Microdot-BNC Cable, 3 m

## Optional items

### Power Modules for Pre-polarized Ear Simulators and Microphones

<a href="#">GRAS 12AL</a>	1-Channel CCP Power Module with A-weighting filter
<a href="#">GRAS 12AQ</a>	2-Channel Universal Power Module with signal conditioning and PC interface

### For Ear Simulator Calibration

<a href="#">GRAS 42AP</a>	Intelligent Pistonphone (250 Hz or 251.2 Hz, 114 dB +/- 0.05 dB)
<a href="#">GRAS 42AA</a>	Pistonphone (250 Hz, 114 dB +/- 0.08 dB)

### Pinna Simulators

<a href="#">GRAS KB5000</a>	Large Right Anthropometric Pinna 35 Shore 00
-----------------------------	--

<a href="#">GRAS KB5001</a>	Large Right Anthropometric Pinna 35 Shore 00
<a href="#">GRAS KB0060</a>	KEMAR Small Right Ear 55 Shore 00
<a href="#">GRAS KB0061</a>	KEMAR Small Left Ear 55 Shore 00
<a href="#">GRAS KB0065</a>	KEMAR Large Right Ear 55 Shore 00
<a href="#">GRAS KB0066</a>	KEMAR Large Left Ear 55 Shore 00
<a href="#">GRAS KB1060</a>	KEMAR Small Right Ear, 35 Shore 00
<a href="#">GRAS KB1061</a>	KEMAR Small Left Ear 35 Shore 00
<a href="#">GRAS KB1065</a>	KEMAR Large Right Ear 35 Shore 00
<a href="#">GRAS KB1066</a>	KEMAR Large Left Ear 35 Shore 00
<a href="#">GRAS KB0090</a>	KEMAR Large Right Ear (VA-Style/SQ) 55 Shore 00
<a href="#">GRAS KB0091</a>	KEMAR Large Left Ear (VA-Style/SQ) 55 Shore 00
<a href="#">GRAS KB1090</a>	KEMAR Large Right Ear (VA-Style) 35 Shore 00
<a href="#">GRAS KB1091</a>	KEMAR Large Left Ear (VA-Style) 35 Shore 00

## Ear Mould Simulators

<a href="#">GRAS KB0110</a>	Ear Mould Simulator for 2 mm Inner diameter tubing
<a href="#">GRAS KB0111</a>	Ear Mould Simulator for 3 mm Inner diameter tubing

## Ear Canal Extension and Microphone Holder Kits (kits with 2 pcs and O-rings)

<a href="#">GRAS RA0237</a>	Straight Ear Canal Extension Kit for KEMAR
<a href="#">GRAS RA0238</a>	VA-tapered Ear Canal Extension Kit for KEMAR
<a href="#">GRAS RA0239</a>	Ear canal Extension Kit w. silicone lining for KEMAR
<a href="#">GRAS RA0240</a>	Holder for long 1/2" microphone Kit for KEMAR
<a href="#">GRAS RA0241</a>	Holder for short 1/2" microphone Kit for KEMAR
<a href="#">GRAS RA0243</a>	Holder for 1/2" microphone Kit for KEMAR
<a href="#">GRAS RA0244</a>	O-ring kit for KEMAR, 2 pcs.
<a href="#">GRAS RA0249</a>	Straight Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test

GRAS RA0250	Tapered Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test
-------------	---

## KEMAR Retrofit Kit for Binaural Hearing Aid Test

[GRAS RA0251](#)

KEMAR Retrofit Kit for Binaural Hearing Aid Test:  
The Kit includes Ear Holder Plates, mounting bolts and the RA0249 and RA0250 Ear Canal Extension Kits. Included items are made of POM, Nylon and Teflon.

## Extension Cables

GRAS AA0034	BNC-BNC Cable, 2 m
-------------	--------------------

[GRAS AA0035](#)

BNC-BNC Cable, 3 m

GRAS AA0036	BNC-BNC Cable, 5 m
-------------	--------------------

[GRAS AA0037](#)

BNC-BNC Cable, 10 m

GRAS AA0039-CL	BNC-BNC Cable, Customized Length, xxxx cm
----------------	---

## Flight Case

GRAS KM0094	PELI Case for KEMAR
-------------	---------------------

## Stand for KEMAR

GRAS AL0026	Loudspeaker stand for KEMAR, Ø 35 mm
-------------	--------------------------------------

## Miscellaneous

GRAS KB0000	KEMAR Handbook
-------------	----------------

GRAS KB0010	T-Shirt for KEMAR
-------------	-------------------

GRAS Sound & Vibration reserves the right to change accessories without notice.



# GRAS Worldwide

Subsidiaries and distributors in more  
than 40 countries

**HEAD OFFICE, DENMARK**  
**GRAS SOUND & VIBRATION**  
Skovlytoften 33  
2840 Holte  
Denmark  
Tel: +45 4566 4046  
[www.grasacoustics.com](http://www.grasacoustics.com)  
[gras@grasacoustics.com](mailto:gras@grasacoustics.com)

**USA**  
**GRAS SOUND & VIBRATION**  
5750 S.W. Arctic Drive  
Beaverton, OR 97005  
Tel: 503-627-0832  
Toll Free: 800-231-7350  
[www.grasacoustics.com](http://www.grasacoustics.com)  
[sales-usa@grasacoustics.com](mailto:sales-usa@grasacoustics.com)

**UK**  
**GRAS SOUND & VIBRATION**  
Unit 115, Gibson House,  
Ermine Business Park, Huntingdon,  
Cambridgeshire, PE29 6XU  
Tel: +44 (0) 7762 584 202  
[www.grasacoustics.com](http://www.grasacoustics.com)  
[sales-uk@grasacoustics.com](mailto:sales-uk@grasacoustics.com)

**CHINA**  
**GRAS SOUND & VIBRATION**  
Room 303, Building T6  
Hongqiaohui, 990, Shenchang Road  
Minhang District, Shanghai  
China. 201106  
Tel: +86 21 64203370  
[www.grasacoustics.cn](http://www.grasacoustics.cn)  
[cnsales@grasacoustics.com](mailto:cnsales@grasacoustics.com)



## About GRAS Sound & Vibration

GRAS is a worldwide leader in the sound and vibration industry. We develop and manufacture state-of-the-art measurement microphones and related equipment for industries where acoustic measuring accuracy and repeatability are of the utmost importance. This includes applications and solutions for customers within the fields of aerospace, automotive, audiology, consumer electronics and other highly demanding industries. GRAS microphones are designed to live up to the high quality, durability and accuracy that our customers have come to expect, trust and require.

GRAS Sound & Vibration is represented through subsidiaries and distributors in more than 40 countries and is part of Axiometrix Solutions, a leading test solutions provider comprised of globally recognized measurement brands. Read more at [www.grasacoustics.com](http://www.grasacoustics.com)

[grasacoustics.com](http://grasacoustics.com)

**GRAS**  
An Axiometrix Solutions Brand