GRAS 45BB-15

KEMAR with Hi-Res Ear Simulators for Test of Ear- and Headphones, 2-Ch LEMO





Connection: Traditional Power Supply (200 V/LEMO)

Channel(s): 2 ANSI: S3.36, S3.25 IEC: 60318-7

ITU-T Rec. P.57 Type 3.3, based on ITU-T

Rec. P.58

The 45BB-15 KEMAR is a manikin configured with externally polarized hi-res ear simulators and anthropometric pinnae for dual-channel ear- and headphone test. Its corresponding CCP equivalent is the GRAS 45BB-16 KEMAR.



Technology

GRAS 45BB-15 KEMAR with Hi-Res Ear Simulators for Test of Ear- and Headphones, 2-Ch LEMO

Introduction

The KEMAR head and torso simulator was introduced by Knowles in 1972 and quickly became the industry standard for hearing-aid manufacturers and research audiologists (visit KEMAR.us to read the full story). It is based on worldwide average human male and female head and torso dimensions. It meets the requirements of ANSI \$3.36/ASA58-2012 and IEC 60318-7:2017.

The GRAS 45BB KEMAR has the same dimensions and acoustical properties as the original KEMAR but has been developed further by GRAS to meet the industry's demand for realistic measurements of hearing aids, headphones, and headsets. It provides acoustic diffraction similar to that encountered around the median human head and torso, both in the proximity and in the far-field.

As all the preconfigured 45BB KEMARs consist of the same basic 45BB KEMAR Non-configured, plus a set of application-specific accessories. The full information about a given KEMAR configuration is obtained by combining the information about the 45BB KEMAR Non-configured and the information for a given configured version as found in the present text. Read about the non-configured KEMAR here.

Design

The 45BB-15 is a KEMAR head and torso for 2-channel ear and headphone test, with externally polarized hi-res audio ear simulators and anthropometric pinnae.

It is delivered fully configured, individually calibrated and ready for use. In addition to a system calibration certificate, a USB flash memory with simulation data is included.

The main configuration specific components of the 45BB-15 are the GRAS RA0403 Hi-Res Ear Simulator

and the KB5000/KB50001 Anthropometric Pinnae.

The Hi-Res Ear Simulator

The acoustic input impedance of the RA0403 Hi-Res Ear Simulator closely resembles that of the human ear and, as a result, loads a sound source in very much the same way. It embodies a number of carefully designed volumes connected via well-defined and precisely tuned resistive grooves. In an equivalent electrical circuit, capacitors would represent the volumes, and inductance and resistance would represent respectively air mass and air flow within the resistive groves.

The RA0403 Hi-Res Ear Simulator mitigates the limited usefulness of the standard IEC60318-4 ear simulator above 10 kHz. The steep resonance at 13.5 kHz has been replaced by a much-dampened resonance and the useful frequency range is now extended to 50 kHz within a narrow tolerance band. It complies with IEC60318-4 and its acoustic transfer impedance is within the tolerance band specified by IEC60318-4. From 10 to 20 kHz the transfer impedance is within ± 2.2 dB, from 20 kHz to 50 kHz it is within ±3.2 dB, resulting in much improved repeatability. Also, realistic THD measurements are now possible.

It is measured and calibrated according to IEC60318-4/ITU-T Recommendation P.57 and delivered with a calibration chart specifying its sensitivity and frequency response.

It is delivered with a built-in <u>GRAS 40BP</u> 1/4" externally polarized pressure microphone.

Read more about RA0403 here.

The Anthropometric Pinna
Compared to the standardized pinna, the
anthropometric pinna embodies several
improvements to the concha and ear canal,
combined with increased collapsibility of the helix,



Technology

GRAS 45BB-15 KEMAR with Hi-Res Ear Simulators for Test of Ear- and Headphones, 2-Ch LEMO

and improved mounting. It is made of soft silicone, 35 Shore 00 hardness.

The external shape of the pinna is identical to that of the standardized KEMAR pinna, but concha and ear canal have been modified so that they closely mimic the properties of a real human ear. The ear canal has been extended and is now an integral part of the pinna which seals directly against the ear simulator. Like the human ear, the ear canal has the 1st and 2nd bend, and the interface with the concha is oval. Fit and insertion consistency are much improved over the cylindrically or conically shaped ear canal extensions that are used with the standard pinna.

The flexibility of the outer ear has been improved, and when mounting supra-aural and circum-aural headphones the pinna now collapses against the head very much like a human ear.

In addition to the traditional push mounting from the outside, the pinna is secured with two screws from the inside of KEMAR's head. These two screws ensure that the pinna is held firmly in place. Therefore, it seals perfectly against the ear simulator and the head, and it is possible to mount and dismount DUTs repeatedly without compromising the seal.

Read more about the Anthropometric Pinnae here.

Typical Applications

The anatomical shape of the pinna makes it possible to achieve a very good fit and sealing with anatomically shaped in-ear transducers.

Controlling the insertion-depth is easy, leading to good insertion consistency and highly improved repeatability and accuracy of measurements.

The improved fit and seal also mean that the low-frequency response is improved. It will allow you to

reproduce bass notes, as well as effectively measure (active & passive) attenuation.

With the hi-res ear simulator, it is now possible to make reproducible measurements up to 50 kHz.

The 45BB-15 KEMAR is ideal for accurate and repeatable hi-res testing of hearing aids, headphones, earphones and in-ear hearing protectors.

Read more about the advantages of the Hi-Res Audio Ear Simulator here.

Performance and warranty

KEMAR is made of components from our standard portfolio and is manufactured of high-quality material and branded parts that were chosen and processed to ensure life-long stability and robustness. This enables us to offer 2 years warranty against defective materials and workmanship.

Exceptions: Microphones included in KEMAR as for these our normal 5-year warranty apply. The warranty period for cables is 6 months.



Specifications

GRAS 45BB-15 KEMAR with Hi-Res Ear Simulators for Test of Ear- and Headphones, 2-Ch LEMO

Connector type		3 m 7-pin LEMO
Set sensitivity @ 250 Hz (±2 dB)	mV/Pa	1.6
Theoretical dynamic range lower limit with GRAS preamplifier	dB(A)	44
Theoretical dynamic range upper limit with GRAS preamplifier @ +120 V / ±60 V power supply	dB	169
Resonance frequency	kHz	13.5
Temperature range, operation	°C / °F	-30 to 60 / -22 to 140
Temperature range, storage	°C / °F	-40 to 65 / -40 to 149
Humidity range non condensing	% RH	0 to 95%
ANSI standard		S3.36, S3.25
IEC standard		60318-7
Weight	g / oz	11.45 k / 404





Included items

GRAS 45BB	KEMAR Head & Torso, Non-configured
GRAS KB5000	Large Right Anthropometric Pinna 35 Shore 00
<u>GRAS KB5001</u>	Large Left Anthropometric Pinna 35 Shore 00
GRAS RA0403	Hi-Res Ear Simulator (2 pcs)
GRAS GR1874	Ear Simulator Holder
GRAS GR0408	External Ear Canal
GRAS GR0409	Union Nut
GRAS 26AS-S3	1/4" Preamplifier, Short version with 0.4 m Cable (2 pcs)
<u>GRAS AA0008</u>	LEMO 7-pin - LEMO 7-pin Cable, 3 m (2 pcs)

Optional items

Power Modules for Externally Polarized Ear Simulators and Microphones

GRAS 12AA	2-Channel Power Module with gain, filters and SysCheck generator
GRAS 12AQ	2-Channel Universal Power Module with signal conditioning and PC interface

For Ear Simulator Calibration

GRAS 42AA	Pistonphone (250 Hz, 114 dB +/- 0.08 dB)
GRAS 42AP	Intelligent Pistonphone (250 Hz or 251.2 Hz, 114 dB +/- 0.05 dB)

Pinna Simulators

GRAS KB0060	KEMAR Small Right Straight Pinna 55 Shore 00
GRAS KB0061	KEMAR Small Left Straight Pinna 55 Shore 00
GRAS KB0065	KEMAR Large Right Straight Pinna 55 Shore 00
GRAS KB0066	KEMAR Large Left Straight Pinna 55 Shore 00
GRAS KB1060	KEMAR Small Right Straight Pinna, 35 Shore 00
GRAS KB1061	KEMAR Small Left Straight Pinna 35 Shore 00



Ordering info

GRAS KB1065	KEMAR Large Right Straight Pinna 35 Shore 00
GRAS KB1066	KEMAR Large Left Straight Pinna 35 Shore 00
GRAS KB0090	KEMAR Large Right Tapered Pinna (VA-Style/SQ) 55 Shore 00
GRAS KB0091	KEMAR Large Left Tapered Pinna (VA-Style/SQ) 55 Shore 00
<u>GRAS KB1090</u>	KEMAR Large Right Tapered Pinna (VA-Style) 35 Shore 00
GRAS KB1091	KEMAR Large Left Tapered Pinna (VA-Style) 35 Shore 00

Ear Mould Simulators

GRAS KB0110	Ear Mould Simulator for 2 mm Inner diameter tubing
GRAS KB0111	Ear Mould Simulator for 3 mm Inner diameter tubing

Ear Canal Extension and Microphone Holder Kits (kits with 2 pcs and O-rings)

GRAS RA0250	Tapered Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test
GRAS RA0237	Straight Ear Canal Extension Kit for KEMAR
GRAS RA0238	VA-tapered Ear Canal Extension Kit for KEMAR
GRAS RA0239	Ear Canal Extension Kit w. silicone lining for KEMAR
GRAS RA0240	Holder for long 1/2" Microphone Kit for KEMAR
GRAS RA0241	Holder for short 1/2" Microphone Kit for KEMAR
GRAS RA0243	Holder for 1/4" Microphone Kit for KEMAR
GRAS RA0244	O-ring kit for KEMAR, 2 pcs.
GRAS RA0249	Straight Ear Canal Extension Kit for KEMAR, made of POM, for binaural hearing aid test

KEMAR Retrofit Kit for Binaural Hearing Aid Test

GRAS RA0251	KEMAR Retrofit Kit for Binaural Hearing Aid Test. The Kit includes Ear Holder Plates, mounting bolts and the RA0249 and RA0250 Ear Canal Extension Kits. Included items are made of POM, Nylon and Teflon.
GRAS RAU251	· · · · · · · · · · · · · · · · · · ·



Ordering info

Extension Cables

GRAS AA0008	LEMO 7-pin - LEMO 7-pin Cable, 3 m
GRAS AA0009	LEMO 7-pin - LEMO 7-pin Cable, 10 m

Flight Case

GRAS KM0094	PELI Case for KEMAR

Simulation Model of KEMAR

GRAS KB3000	3D Simulation Model of KEMAR with large pinnae, stp file
GRAS KB3001	3D Simulation Model of KEMAR with small pinnae, stp file
GRAS KB3002	3D Simulation Model of KEMAR with anthropometric pinnae, stp file

Stand for KEMAR

GRAS AL0026	Stand for KEMAR, Ø 35 m

Miscellaneous (incl. in 45BB)

GRAS KB0000	KEMAR Handbook
GRAS KB0010	T-Shirt for KEMAR

GRAS Sound & Vibration reserves the right to change specifications and accessories without notice.



GRAS Worldwide

Subsidiaries and distributors in more than 40 countries

HEAD OFFICE, DENMARK

GRAS SOUND & VIBRATION

Skovlytoften 33 2840 Holte Denmark Tel: +45 4566 4046 www.GRASacoustics.com gras@grasacoustics.com

USA

GRAS SOUND & VIBRATION

9290 SW Nimbus Avenue Beaverton, OR 97008 Tel: 503-627-0832 Toll Free: 800-231-7350 www.GRASacoustics.com sales-usa@grasacoustics.com

UK

GRAS SOUND & VIBRATION

Unit 115, Gibson House, Ermine Business Park, Huntingdon, Cambridgeshire, PE29 6XU Tel: +44 (0) 7762 584 202 www.GRASacoustics.com sales-uk@grasacoustics.com

CHINA

GRAS SOUND & VIBRATION

Room 315, RuiBo Center(T1) Lane683, Shenhong Rd, Minhang District, Shanghai, China, 201107 Tel: +86 21 64203370 www.GRASacoustics.cn cnsales@grasacoustics.com



About GRAS Sound & Vibration

GRAS is a worldwide leader in the sound and vibration industry. We develop and manufacture state-of-the-art measurement microphones and related equipment for industries where acoustic measuring accuracy and repeatability are of the utmost importance. This includes applications and solutions for customers within the fields of aerospace, automotive, audiology, consumer electronics and other highly demanding industries. GRAS microphones are designed to live up to the high quality, durability and accuracy that our customers have come to expect, trust and require.

GRAS Sound & Vibration is represented through subsidiaries and distributors in more than 40 countries and is part of Axiometrix Solutions, a leading test solutions provider comprised of globally recognized measurement brands. Read more at www.grasacoustics.com

GRAS

An Axiometrix Solutions Brand

grasacoustics.com